

Ozone Accessories

Our standard fitting size is for 4x6 mm flexible tubing (FEP, PTFE, etc.). Other fitting types and sizes on request.

Fittings, Reducers, Tubing

F 3x5-M5	F 3x5-M5-OR	F 4x6-M5	F 3x5-1/8	F 4x6-1/8	F 4x6-1/8-SS

order number	description
F 3x5-M5	fitting for 3x5 mm (or 1/8" x 3/16" resp.) FEP tubing, M5 thread, SS
F 3x5-M5-OR	same as F 3x5-M5, with KALREZ® O-ring on mounting side
F 4x6-M5	fitting for 4x6 mm FEP tubing, M5 thread, SS
F 3x5-1/8	fitting for 3x5 mm (or 1/8" x 3/16" resp.) FEP tubing, G1/8 thread, aluminum, black anodised
F 4x6-1/8	fitting for 4x6 mm FEP tubing, G1/8 thread, aluminum, black anodised
F 4x6-1/8-SS	fitting for 4x6 mm FEP tubing, G1/8 thread, SS
nut 3x5	additional nuts for the above fittings may be ordered separately
nut 4x6	additional nuts for the above fittings may be ordered separately

PMU 3x5-3x5 PMU 4x6-4x6 AD/PMU 3x5-4x6	PMU 3x5-SL1/4	TEE 3x5 TEE 4x6	Test Connector			

order number	description
PMU 3x5-3x5	panel mount union for 3x5 FEP tubing, hole 10 mm, max. wall thickness 5 mm, SS
PMU 4x6-4x6	panel mount union for 4x6 FEP tubing, hole 10 mm, max. wall thickness 5 mm, SS
AD/PMU 3x5-4x6	same as above, panel mount reducer
PMU 3x5-SL1/4	panel mount reducer union, 1/4" LET-LOK (Swagelok interchangeable) to 3x5 mm FEP tubing, hole 10 mm, max. wall thickness 5 mm, SS
TEE 3x5	Tee connection with fittings for 3x5 mm FEP tubing, AL, SS
TEE 4x6	Tee connection with fittings for 4x6 mm FEP tubing, AL, SS
Test Connector	for connecting a test analyser in parallel, different fitting types and sizes on request

TU	FLEXA 8x10

order number	description	
TU 2.5x4	FEP tubing, 2.5x4 mm, transparent	per m
TU 3x5	FEP tubing, 3x5 mm (1/8" x 3/16"), transparent	per m
TU 4x6	FEP tubing, 4x6 mm, transparent	per m
TU 1/4x5/32	FEP tubing, 1/4" x 5/32", transparent	per m
FLEXA 8x10	flexible SS tubing ID 7.5 mm, for protecting FEP tubing	per m

LOP_001_EN_2024-02-01